

Pupillometry

APD-400



- 1 Break with the traditional way of measurement
- 2 Built-in HD camera
- 3 4.3 inch LCD screen, more intuitive observation
- 4 Built-in 3000mA rechargeable lithium battery, single charge for one week
- 5 LED light source, measurement step adjustable
- 6 With automatic calibration function

Specifications: APD-400

Binocular Pupillary Distance	45~82 Mm
Monocular Pupillary Distance	22.5~41 Mm
Maximum allowable error of pupil	±0.5 Mm
distance indication	
Maximum allowable error of left and right	± 0.5 Mm
asymmetries	
Distance of Target	30 Cm~∞
Power Source: Voltage	DC 3v
Specification	Lithium battery
Size	230mm(L)× 170mm(W)× 65mm(H)
Weight	0.8 Kg



MERCOFrames
OPTICAL CORP

✉ salesusa@mercoframes.net

🌐 www.mercoframes.com

📍 5555 NW 74 AVE.
MIAMI, FL. 33166

☎ P: 305-882-0120
F: 305-882-0140